

Single Use Microfibre Mop + Adapter



The smart choice for hygienic
and efficient floor care



- ✓ Removes 99,99% bacteria
- ✓ Enhanced cleaning power
- ✓ Versatile usage
- ✓ Convenient & hygienic
- ✓ 100% biodegradable
- ✓ Secure fit & easy handling
- ✓ Flexible compatibility
- ✓ 100% Mibrofibre

Effective, hygienic, and versatile cleaning

The Vikan Single Use Microfibre Mop Kit is designed for hygiene-critical environments where washing reusable mops is not an option, offering superior cleaning performance, convenience, and flexibility. Ideal for healthcare facilities, it provides a practical cleaning solution in hospitals and care homes. In retail and hospitality settings, it ensures fast and effective cleaning in shops, restaurants, and hotels. Additionally, it is perfect for industrial and craft rooms, providing efficient dust control in workshops and other high-traffic areas. Whether used damp, wet, or dry, this kit is a highly effective alternative to washable mop systems.

Preparations

- **Dry:** Use the mops as they are.
- **Damp mopping:** Spray water on the mop.
- **Wet mopping:** Use 3 dl water to prepare up to 5 mops at once. Add extra water to the adapter if extra moisture is requested.



How it works

1. Attach the single-use microfibre mop direct to the Vikan mop frame. Use the adapter in between when extra moisture and/or comfort is requested.
2. Choose your preferred cleaning method – dry, damp, or wet as described above. For added moisture, press slightly on the adapter to release water.
3. Place your foot on the edge of the mop, move the mopframe upwards/ toward opposite side to remove the mop.
4. After use, dispose of the mop responsibly to maintain optimal hygiene.



Item numbers

- 65204050: Single use, Microfiber mop, 40 cm, White
- 65204051: Single Use, Microfibre Mop kit 50pc +1 Adapter, 40cm
- 65206050: Single use, Microfiber mop, 60 cm, White
- 65206051: Single Use, Microfibre Mop kit 50pc +1 Adapter, 60cm

Visit us at vikan.com

E-mail: sales@vikan.co.uk

Phone: +44 (0)1793 716 760

